

# FULL FACE MASK

Mod. TR 82

P/N 112190000

Full face mask, negative pressure, with threaded connector to **EN 148-1** made of:

- Moulded face blank
- Wide visibility panoramic visor
- Group that holds in one single body the thread connection, the exhalation valves, the inhalation valve and the speech device.
- Inner nose cup
- Head harness five straps
- Neck tape

The mask can be used with negative pressure devices provided with the same threaded connector to EN 148-1, such as filters, air lines AC190, etc.



## TECHNICAL DATA

### Breathing Resistance

Test flow	Inhalation (mbar)		Exhalation (mbar)	
	Standard	Measured	Standard	Measured
25 cycles/min x 2 l/stroke	≤ 2.5	1.3	≤ 3.0	1.8
30 l/min	≤ 0.5	0.1		
95 l/min	≤ 1.5	0.7		

### Inward Leakage

Test gas	Max admitted inw. Leakage (%)	Measured Penetration (%) (10 subjects average)
SF6	0.05	< 0.03

### Limitations for use

The mask cannot be used with positive pressure SCBAs nor with devices not provided with the same connector to EN 148-1.

### CLASSIFICATION

Full Face Mask, Class 3 to **EN 136:1998** and according to Regulation (EU) **2016/425 (PPE)**.



# FULL FACE MASK

Mod. TR 82

P/N 112190000

## MARKING



## MATERIALS

Face Blank:	EPDM
Visor:	Polycarbonate
Head harness:	EPDM
Nose Cup:	TPE
Neck strap:	PVC

## STORAGE

Store at temperatures between -20 and +50 °C and RH <80%

## WEIGHT

570 g (1,30 lb) approximately.

## DIMENSIONS/PACKAGING

The mask is delivered in a PE bag into a single carton box, dimensions 230x175x125 mm (9.05 x 6.89 x 4.92 in).  
Masks come in a multiple 6 pieces carton, dimensions 470x390x200 mm (18.50 x 15.35 x 7.87 in).

---

**For more information please check the notes along with the products or the ones published on the website: [www.spasciani.com](http://www.spasciani.com)**

*NOTE: SPASCIANI SpA does not take any responsibility for any possible and unintentional mistake and reserve the faculty of modify materials and technical characteristics of its products at any time and without any notice.*